


32" Pixel Plus Flex TV

MATCH  **LINE**



- Real Flat Black Line S
- Pixel Plus
- 100Hz Digital Scan
- Digital Natural Motion
- Digital Crystal Clear
- Dolby Pro-Logic 3D Surround
- 60 W RMS
- 6 On Board Speakers
- Compass Graphical User Interface
- Pause Live TV
- Instant Replay
- Multi Event Programming
- Commercial Skip
- 1200 Page Hypertext
- Full Dual Screen
- Top Controls
- Cinemalink
- Side Connections
- Matching Stand Available

**REAL
FLAT**



PIXEL PLUS

DIGITAL
NATURAL MOTION

DIGITAL
CRYSTAL CLEAR



**active
control**
+ Light Sensor

easy  1200 P



Let's make things better.



PHILIPS

32" Pixel Plus Flex TV



This Time Machine widescreen brings the best in picture quality linked to the ultimate in convenience. Features a Real Flat screen enhanced by Digital Natural Motion and Pixel Plus creating fantastic picture detail and depth. A massively enhanced TV memory allows you to record programmes at the push of a button, pause live TV, then resume watching as if live, later even if the programme you resume watching is still taking place. Instant replay and commercial skip also make this TV a technical wizard. 6 speakers combined with Dolby 3D Surround and the optional 2 extra cordless speakers create a true-to-life home cinema experience. Full Dual Screen allows you to view 2 pictures side by side and record programmes whilst watching something else. Comes with matching stand.

Technical specifications

Picture

- Screen Size: 32" (82 cm)
- Visible screen size: 76 cm (32")
- Picture Tube: Real Flat Black Line S
- Pixel Plus
- 100Hz Digital Scan
- Digital Natural Motion
- Digital Crystal Clear
- Dynamic Scavem
- Dynamic Auto Focus
- Active Control + Light Sensor
- Widescreen Plus
- Picture Freeze

Sound

- Sound Power: 60 W RMS
120 W Music Power
- Dolby Pro-Logic 3D Surround
- 6 On Board Speakers
- Subwoofer
- Digital Signal Processing

Ease of Use Installation

- 100 Preset channels
- Autostore
- Fine Tuning
- Sorting
- Smart ATS and ACI

Ease of Use Utilisation

- Compass Graphical User Interface
- Menu Help Function
- Top Controls
- RC 4301 (suitable for VCR/DVD/SAT/AUDIO/CD-R)
- Program List
- Smart Picture Control: Soft, Natural, Rich, Multimedia, Personal
- Smart Sound Control: Movie, Speech Music, Personal
- AVL
- Dual I-II
- 6 Wide screen modes: 4:3, Zoom 14:9, Zoom 16:9
Subtitle Zoom, Super Zoom, Widescreen
- Subtitle and Heading shift
- Autoformat / Autoscreen fit (incl. WSSB)
- Smart Clock
- Sleep Timer
- Child Lock
- Picture Tilt Control

Connections

Side

- S-Video (Y/C) in
- CVBS Video in
- Audio L/R (cinch/RCA) in
- Headphone Jack 3,5 mm out

Back

- Euro A/V connector Ext1 (RGB in, CVBS in/out)
- Euro A/V connector Ext2 (RGB in, S-Video in/out, CVBS in/out)
- Euro A/V connector Ext3 (CVBS in)
- Euro A/V connector Ext4 (CVBS in)
- Stereo Audio out (cinch) Constant/Variable level
- Surround sound out (cinches and click-fits)
- Subwoofer sound out (cinches)

Information

- 1200 Page Text level 2.5 with Habit Watch
- Hypertext: instant search via word and page catching
- Word Search: Free format searching in teletext data
- Program Information Line
- NexTVView Level 3
- Easy Link : Pre-set download, WYSIWYR, One Touch Record
- NexTVView Link
- Cinemalink AV Control System
- 2 Tuner - Full Dual Screen
- Mosaic
- Replay
- Zoom 16x

Reception

- Tuning System: PLL digital tuning
- Tuner: VHF, UHF, S-Channel, Hyperband
- Aerial Input: 75 ohm Coaxial
- TV System: See table
- Stereo System: See table
- Video Playback: NTSC 4.43/3.58

Miscellaneous

- Mains: AC 220-240V +/- 10%
- Power Consumption: 180W Normal Operation
< 1W Stand by
- Set Weight: 32" - 59,3 kg
- Weight Incl. Packaging: 32" - 847x549x539 mm
- Set Dimension (WxHxD): 32" - 847x549x539 mm
- Box Dimension (WxHxD): 32" - 951x701x700 mm
- TV Colour: Precision Silver (10888)

Product highlights

Real Flat Black Line S

Philips TV picture tube provides non-distorted picture quality, while offering a wider viewing angle without light reflections. Thanks to the highly pigmented phosphors, the brightness and contrast performance are considerably improved compared to conventional picture tubes.

Pixel Plus

Uses the power of the Pixel Plus processor to create 33 % more lines and double the number of Pixels on each line. The result is razor sharp pictures with incredible detail and depth, every time from any source.

Digital Natural Motion

Building upon 100 Hz technology Philips invented Digital Natural Motion to eliminate juddering effects that are visible with moving picture content. Digital Natural Motion estimates motion in the picture and corrects juddering movements in both broadcast and movie material (DVD). Smooth motion reproduction and excellent sharpness are the result.

Digital Crystal Clear

A unique package of picture innovations including Combfilter, Scavem, Dynamic Contrast, Color Enhancement and Luminance Transient Processing. Digital Crystal Clear, using 10 bit processing, offers 30% more contrast, natural colors and a high level of detail.

Dolby Pro-Logic 3D Surround

Using full Dolby Pro-Logic decoding, 3D Surround offers a cinema surround sound experience with integrated centre speaker, and without cables and rear speakers.

1200 Page HyperText & Wordsearch

Advanced Teletext featuring based upon the new Compass GUI with navigation functions Wordsearch and HyperText. In HyperText select any word within the teletext magazine and this system will find all other mentions of this word within teletext for that channel. Wordsearch is similar but you have the freedom to type in, using the remote control, a word of your choosing.

Pause live TV

Instant Recording at the touch of 1 button. Resume watching as if live, 10, 20 or 60 minutes later.

Instant Replay

Instant Play Back of last 6 seconds of action.

Multi Event Programming

Transfer any recording to a VCR or DVD Recorder to create a permanent record for your collection.

Commercial Skip

On any recording one button allows 30 second skipping of the programme to omit commercials.

version		stereo system						transmission system					
		2CS DK	NICAM DK	2CS BG	NICAM BG	NICAM I	NICAM LL'	PAL BG	PAL DK	PAL I	SECAM BG	SECAM DK	SECAM LL'
32PW9768	/05	•	•	•	•	•	•	•	•	•	•	•	•
32PW9768	/12	•	•	•	•	•	•	•	•	•	•	•	•
32PW9768	/58	•	•	•	•	•	•	•	•	•	•	•	•

Predecessor : --
Chassis : EMG Top
Introduction : Year 2003

Features and specifications subject to change without notice

04/2002

Let's make things better.



PHILIPS